





Small, portable, and easy to carry

Transcend's DrivePro 20 dashcam is designed for motorcycles and scooters. Its compact size makes it easy to install on a helmet. By pressing the power button for 3 seconds, the DrivePro 20 is ready to hitch a ride with you!



STARVIS™ high-sensitivity image sensor

The DrivePro 20's 140° wide-angle lens is made with a STARVIS™ image sensor and Wide Dynamic Range (WDR) technology to capture high-resolution images with superb, rich color even in low light. Supporting Full HD 1080P recording at 60fps, the camera captures every important detail, including license plates.

Note: STARVIS™ is a trademark of Sony Corporation.



Rugged and durable design

The DrivePro 20 is designed with an aluminum exterior to withstand harsh weather conditions, making it ideal for outdoor recording. It is IP68 rated, offering full protection against dust and water. It also meets rigorous US military drop-test standards for shock resistance.

Note: The DrivePro 20 was tested under controlled laboratory conditions and given a rating of IP68 under IEC standard 60529. Splash, water, and dust resistance are not permanent conditions and resistance may decrease as a result of normal wear. Product must be clean and dry before use. Liquid damage is not covered under warranty.





Motorcycle Dashcam DrivePro 20

Features

- STARVIS™ high-sensitivity image sensor
- 1080P Full HD recording at 60 fps
- Built-in Wi-Fi function for mobile live streaming
- Emergency recording prevents overwriting of the current recorded file
- IP68 rated, resistant to dust, water, and shock



DrivePro Toolbox

DrivePro Toolbox helps you play and manage videos recorded on your DrivePro dashcam without installing any separate codecs.



DrivePro App

DrivePro App is designed for use with DrivePro dashcams featuring Wi-Fi connectivity. Stream videos and adjust settings from your mobile device, and download footage for on-the-go!

Specifications

Appearance

Dimensions	90.2 mm x 30 mm x 30 mm (3.55" x 1.18" x 1.18")
Camera Weight	74 g (2.6 oz)
Camera Holder Weight	20 g (0.7 oz)

Interface

USB Type	micro USB to USB Type A
Connection Interface	USB 2.0
Wi-Fi Protocol	802.11b/g/n

Storage

Capacity 32GB m	nicroSD card included / 64GB microSD card included
-----------------	--

Hardware

Viewing Angle	140° (diagonal)
Aperture	F/2.8

Operating Environment

Operating Temperature	-10°C (14°F) ~ 60°C (140°F)
IP Rating	IP68

Format

Resolution	Full HD 1080P
Frame Rate	60/30 fps
Video Format	MP4 (H.264)

Power

Battery Life (N	Лах.)	2.5 hour(s

Warranty

Certificate	CE / FCC / BSMI / NCC / MIC / KC / RCM / EAC / UKCA
Warranty	Two-year Limited Warranty

Package

Package Contents	Full unit / 32GB microSD memory card / 64GB microSD memory
	card / Adhesive mounting base / Quick Start Guide / Camera holder
	/ micro-USB to USB Type-A cable

Ordering Information

32GB	TS-DP20A-32G
64GB	TS-DP20A-64G

Product specifications are subject to change without notice. Pictures shown may differ from actual products. Total accessible capacity varies depending on operating environment.