



BenQ PD2706UA Monitor PC 68,6 cm (27") 3840 x 2160 Pixel 4K Ultra HD LCD Nero

Marchio : BenQ

Codice prodotto: 9H.LLKL.B.QBE

Nome del prodotto : PD2706UA

BenQ PD2706UA. Dimensioni diagonale schermo: 68,6 cm (27"), Risoluzione del display: 3840 x 2160 Pixel, Tipologia HD: 4K Ultra HD, Tecnologia display: LCD, Tempo di risposta: 5 ms, Rapporto d'aspetto nativo: 16:9, Angolo di visualizzazione (orizzontale): 178°, Angolo di visualizzazione (verticale): 178°. Altoparlanti incorporati. Hub USB integrato, Versione dell'hub USB: 3.2 Gen 1 (3.1 Gen 1). Montaggio standard VESA, Regolazione altezza. Colore del prodotto: Nero



Display		Ports & interfaces	
Display diagonal *	68.6 cm (27")	HDMI *	✓
Display resolution *	3840 x 2160 pixels	HDMI ports quantity	1
HD type *	4K Ultra HD	HDMI version	2.0
Native aspect ratio *	16:9	DisplayPorts quantity	1
Display technology *	LCD	DisplayPort version	1.4
Panel type *	IPS	Headphone out *	✓
Backlight type	LED		
Touchscreen *	✗	Ergonomics	
Display brightness (peak)	400 cd/m²	VESA mounting *	✓
Display brightness (typical)	350 cd/m²	Panel mounting interface	100 x 100 mm
Response time *	5 ms	Cable management	✓
Anti-glare screen	✓	Cable lock slot *	✓
Screen shape *	Flat	Height adjustment *	✓
Aspect ratio	4:3, 16:9	Adjustable height (max)	15 cm
Contrast ratio (typical) *	1200:1	Pivot	✓
Maximum refresh rate *	60 Hz	Pivot angle	-90 - 90°
Viewing angle, horizontal	178°	Swivelling	✓
Viewing angle, vertical	178°	Swivel angle range	275 - 275°
Display number of colours *	1.07 billion colours	Tilt adjustment	✓
Pixel density	163 ppi	Tilt angle range	-5 - 30°
Horizontal scan range	27 - 135 kHz	On Screen Display (OSD)	✓
Vertical scan range	24 - 76 Hz	On Screen Display (OSD) languages	Arabic, Simplified Chinese, Traditional Chinese, German, Dutch, English, Spanish, French, Hungarian, Italian, Japanese, Korean, Polish, Portuguese, Romanian, Russian, Swedish
Display diagonal (metric)	68.5 cm		
High Dynamic Range (HDR) supported	✓		
High Dynamic Range (HDR) technology	High Dynamic Range (HDR) 400, High Dynamic Range 10 (HDR10)		
Colour gamut standard	sRGB	Power	
Colour gamut	99%	Energy efficiency class (SDR) *	G

Display		Power	
sRGB coverage (typical)	99%	Energy efficiency class (HDR) *	G
Performance		Energy consumption (SDR) per 1000 hours *	42 kWh
Flicker-free technology	✓	Energy consumption (HDR) per 1000 hours *	44 kWh
Low Blue Light technology	✓	Power consumption (typical) *	27.5 W
Smart modes	Animation, Black & White, M-Book, ePaper	Power consumption (standby) *	0.5 W
Multimedia		Power consumption (max)	152 W
Number of speakers	2	AC input voltage	100 - 240 V
RMS rated power	5 W	Energy efficiency scale	A to G
Built-in speaker(s) *	✓	European Product Registry for Energy Labelling (EPREL) code	1389781
Built-in camera *	✗	Weight & dimensions	
Design		Width (with stand)	614 mm
Market positioning *	Graphics design	Depth (with stand)	459.4 mm
Product colour *	Black	Height (with stand)	553 mm
Ports & interfaces		Weight (with stand)	10 kg
Built-in USB hub *	✓	Width (without stand)	614 mm
USB hub version	3.2 Gen 1 (3.1 Gen 1)	Depth (without stand)	81.3 mm
USB upstream port type	USB Type-C	Height (without stand)	553.7 mm
Number of USB Type-C upstream ports quantity	1	Weight (without stand)	6.2 kg
USB Type-A downstream ports quantity	3	Packaging content	
USB Type-C downstream ports quantity	1	Stand included	✓
USB Type-C DisplayPort Alternate Mode	✓	Cables included	DisplayPort, HDMI, USB
USB Power Delivery (USB PD)	✓	DisplayPort cable length	1.8 m
USB Power Delivery up to	90 W	HDMI cable length	1.8 m
		Other features	
		Contrast enhancer	✓
		Certification	TUV, Solidworks, calman, Pantone Validated, Pantone SkinTone



4718755090370

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 09-MAR-2025. Prints or copies of Information are only valid on the printed Publication date