

Hisense RQ5P470SAFE frigorifero 4 porte Libera installazione 483 L E Nero

Marchio : Hisense

Codice prodotto: RQ5P470SAFE

Nome del prodotto : RQ5P470SAFE frigorifero 4 porte
Libera installazione 483 L E Nero

Hisense RQ5P470SAFE frigorifero 4 porte Libera installazione 483 L E Nero. Posizionamento dell'apparecchio: Libera installazione, Design del prodotto: Multi porta, Colore del prodotto: Nero. Capacità netta totale: 483 L, Emissione acustica: 37 dB. Capacità netta frigorifero: 304 L. Capacità netta congelatore: 179 L, Posizione del congelatore: Posto in basso, Punteggio: 4*. Classe efficienza energetica: E, Carico di collegamento: 145 W, Tensione di ingresso AC: 220 - 240 V



Design		Freezer	
Appliance placement *	Freestanding	No Frost (freezer) *	✓
Product design *	Multi door	Automatic defrost (freezer)	✓
Product colour *	Black	Freezer number of shelves/baskets *	6
Control type	Touch		
Built-in display *	✓	Ice cube tray	✓
Display type	LED		
Refrigerating medium	R600a		
Performance		Fresh zone	
Total net capacity *	483 L	Fresh zone compartment *	✓
Noise level *	37 dB		
Water dispenser *	✗		
Icemaker *	✗		
Inverter technology	✓		
Fridge		Ergonomics	
Fridge net capacity *	304 L	Door open alarm	✓
No Frost (fridge) *	✓	Castor wheels	✓
Automatic defrost (fridge)	✓	Adjustable feet	✓
Multi-Airflow system (fridge) *	✓	Wi-Fi	✓
Fridge number of shelves/baskets *	3		
Number of vegetable drawers *	2		
Fridge door balconies	6		
Egg balcony	✓		
		Power	
		Energy efficiency class *	E
		Connected load	145 W
		AC input voltage	220 - 240 V
		AC input frequency	50 Hz
		Weight & dimensions	
		Width *	794 mm
		Depth *	698 mm
		Height *	1785 mm

Fridge		Weight & dimensions	
Super Cool function	✓	Weight *	90 kg
Freezer		Packaging data	
Freezer net capacity *	179 L	Package width	842 mm
Freezer position *	Bottom-placed	Package depth	744 mm
Star rating *	4*	Package height	1885 mm
		Package weight	97.9 kg
		Other features	
		Reversible doors	✗
		Adjustable thermostat	✓



6921727078513

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 08-APR-2025. Prints or copies of Information are only valid on the printed Publication date