

Hisense RB390N4AWE frigorifero con congelatore Libera installazione 304 L E Bianco

Marchio : Hisense

Codice prodotto: RB390N4AWE

Nome del prodotto : RB390N4AWE

Hisense RB390N4AWE. Capacità netta totale: 304 L. Cerniera porta: Destra, Tipo di display: LED. Classe climatica: SN-N, Emissione acustica: 39 dB. Capacità netta frigorifero: 207 L, No Frost (frigorifero), Sistema Multi-Airflow (frigorifero), Luce interna, Numero di ripiani frigorifero: 3. Capacità netta congelatore: 97 L, No Frost (congelatore). Classe efficienza energetica: E, Consumo energetico annuo: 243 kWh. Colore del prodotto: Bianco



Design		Fridge	
Appliance placement *	Freestanding	Fridge number of shelves/baskets *	3
Product colour *	White	Number of vegetable drawers *	1
Door hinge	Right	Fridge door balconies	3
Reversible doors	✓	Super Cool function *	✗
Door opening angle	90°	Freezer	
Door assembly	Door slider	Freezer position *	Bottom-placed
Control type	Touch	Freezer net capacity *	97 L
Built-in display *	✓	No Frost (freezer) *	✓
Display type	LED	Freezer interior light	✓
Display placement	Inside	Freezer number of shelves/baskets *	2
Housing material	Steel	Fast freeze function *	✓
Inverter technology	✗	Super freeze function	✓
Recessed handle(s)	✓	Ergonomics	
Performance		Door open alarm	✗
Total net capacity *	304 L	Wi-Fi	✗
Climate class *	SN-N	Power	
Noise emission class *	C	Energy efficiency scale	A to G
Noise level *	39 dB	Energy efficiency class *	E
Icemaker *	✗	Annual energy consumption *	243 kWh
Water dispenser	✗		
Holiday function	✓		

Fridge		Weight & dimensions	
Fridge net capacity *	207 L	Width *	595 mm
Fridge interior light	✓	Depth *	589 mm
Lamp type	LED	Height *	1860 mm
No Frost (fridge) *	✓	Weight *	59 kg
Multi-Airflow system (fridge) *	✓	Packaging data	
		Package width	645 mm
		Package depth	628 mm
		Package height	1935 mm
		Package weight	65 kg



6921727072863

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 17-APR-2025. Prints or copies of Information are only valid on the printed Publication date