

Electrolux LTB1AE24U0 Libera installazione 209 L E Argento

Marchio : Electrolux

Codice prodotto: 925 992 227

Nome del prodotto : LTB1AE24U0

Electrolux LTB1AE24U0. Capacità netta totale: 209 L. Cerniera porta: Destra, Tipo di display: LCD. Classe climatica: SN-ST, Emissione acustica: 39 dB. Capacità netta frigorifero: 165 L, Luce interna, Numero di ripiani frigorifero: 3, Numero di cassetti per verdura: 1. Capacità netta congelatore: 41 L, Capacità di congelamento: 2 kg/24h. Classe efficienza energetica: E, Consumo energetico annuo: 177 kWh. Colore del prodotto: Argento



Design		Congelatore	
Posizionamento dell'apparecchio *	Libera installazione	Posizione del congelatore *	Posto in alto
Colore del prodotto *	Argento	Capacità netta congelatore *	41 L
Cerniera porta	Destra	Capacità di congelamento *	2 kg/24h
Porte reversibili	✓	Autonomia senza energia elettrica *	19 h
Display incorporato *	✓	Punteggio *	4*
Tipo di display	LCD	Numero di ripiani congelatore *	1
Prestazione		Ergonomia	
Capacità netta totale *	209 L	Allarme porta aperta	✗
Classe climatica *	SN-ST	Allarme di temperatura	✗
Classe emissione rumore *	C	Lunghezza cavo	2,5 m
Emissione acustica *	39 dB	Gestione energetica	
Frigorifero		Scala di efficienza energetica	Da A a G
Capacità netta frigorifero *	165 L	Classe efficienza energetica *	E
Luce interna	✓	Consumo energetico annuo *	177 kWh
Tipo di lampada	LED	Carico di collegamento	110 W
Sbrinamento automatico (frigorifero)	✓	Tensione di ingresso AC	230 V
Numero di ripiani frigorifero *	3	Corrente	10 A
Numero di cassetti per verdura *	1	Dimensioni e peso	
		Larghezza *	550 mm
		Profondità *	547 mm
		Altezza *	1434 mm



7332543738106

Catalog Object Cloud



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.