


Datasheet

Item no.1564140

V1_0817_01_en

Outlet socket with protective cap

Rating	12 V/DC 20 A max	Mounting Hole
Contact Resistance	50m ohm Max	F G G G G G G G G G G G G G G G G G G G
Insulation Resistance	DC 500V 100M ohm Mln	
Dielectric Strength	AC 1500V 1 mInute	
Operation Temperature	-20C~85C	



This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.