




# Datasheet

Item no.: 1587688




V1\_0712\_01\_en

## Toggle switch

Rating	20A 12V DC	Mounting Hole		Circuit Diagram	
Contact Resistance	50m ohm Max.				
Insulation Resistance	DC 500V 100M ohm Min.				
Dielectric Strength	AC 1500V 1 minute				
Operation Temperature	-20°C~85°C				
Switch Function	3P SPST ON-OFF (LED)				
LED Color	Yellow				



- 1 HEX NUT ASSY
- 1 SPRING WASHER ASSY
- 1 KNURL NUT ASSY



KEYWAY on "ON"

Tolerances  $\pm 0.3$  Unless Otherwise Specified