

## crimpcontact - ST-06KS020 - 1607581

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



crimpcontact, gedraaid, contactdiameter: 0,6 mm, crimpbereik: 0,14 mm<sup>2</sup>...0,34 mm<sup>2</sup>

### Key commercial data

package_quantity	100
GTIN	4046356272971

### Technical data

#### Algemeen

contactuitvoering	gedraaid
contactdiameter	0,6 mm
soort contact	bus
aansluitmethode	crimpaansluiting
steekcycli mechanisch	50
min. aderdoorsnede	0,14 mm <sup>2</sup>
max. aderdoorsnede	0,34 mm <sup>2</sup>

### classifications

#### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260708
eCl@ss 7.0	27440312
eCl@ss 8.0	27440204

#### ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC000796
ETIM 5.0	EC000796

#### UNSPSC

UNSPSC 6.01	43172015
-------------	----------

# crimpcontact - ST-06KS020 - 1607581

## classifications

### UNSPSC

UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

## approvals

---

GOST /

---

### Approval details



## accessories

SF-Z0054 - 1615585



## Drawings

© Phoenix Contact 2014 - all rights reserved  
<http://www.phoenixcontact.com>