

## Kabelconnectoren - CA-17S1N8A8007S - 1619512

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



kabelconnector, recht, afgeschermd: ja, SPEEDCON-vergrendeling, M23, aantal polen: 17, soort contact: bus, crimpaansluiting, kabeldiameter: 6 mm ... 10 mm

De afbeelding toont de 12-polige productvariant



### Key commercial data

package_quantity	1
GTIN	4046356823432

### classifications

#### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	272607xx
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260702
eCl@ss 7.0	27440102
eCl@ss 8.0	27440102

#### ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002635
ETIM 5.0	EC002635

#### UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

### Drawings

# Kabelconnectoren - CA-17S1N8A8007S - 1619512

Maatschets



# Kabelconnectoren - CA-17S1N8A8007S - 1619512

schematekening

