



Configuratiemodule voor configuratie van hellingtijd, motorbeveiliging, stuurklemmenfunctie voor frequentieregelaar DE1

Type DXE-EXT-SET
Catalog No. 174621
Alternate Catalog No. DXE-EXT-SET

Leveringsprogramma

Beschrijving		Met keuzeschakelaar voor hellingtijd en bedrijfsmodus Met potentiometer voor motorbeveiliging en vaste frequentie
Toepasbaar voor		DE1, DE11
Aansluittechniek		Steekmodule (frontzijde)

Ontwerpverificatie conform IEC/EN 61439

Technische gegevens ontwerpverificatie			
Bedrijfsomgevingstemperatuur min.	°C		-10
Bedrijfsomgevingstemperatuur max.	°C		50

Technische gegevens ETIM 7.0

Laagspanning schakelapparaten (EG000017) / Toebehoren voor frequentieregelaar (EC002025)			
Elektro-, automatiserings- en procesbesturingstechniek / Elektrische aandrijving / Frequentieomvormer / Static frequency converter (accessory) (ecl@ss10.0.1-27-02-31-92 [AFR303003])			
Type toebehoren/onderdelen			Overig

Goedkeuringen

Product Standards			UL 508C; CSA-C22.2 No. 274; IEC/EN61800-3; IEC/EN61800-5; CE marking
UL File No.			E172143
UL Category Control No.			NMMS, NMMS7
CSA File No.			UL report applies to both US and Canada
North America Certification			UL recognized, certified by UL for use in Canada
Specially designed for North America			No
Suitable for			Branch circuits

Afmetingen

