

Auxiliary current switch with test button 1 NO + 1 NC for miniature circuit breaker 5SL, 5SY, 5SP Incorporated switch 5TL1, RCBO 5SU1, FI 5SV (for 5SU1 handle coupler 5ST3805-1 is required)



Versie	
productmerknaam	SETRON
productbenaming	hulpcontact
uitvoering van het product	aanbouwbaar
elektrische levensduur (schakelcycli) / typisch	20 000
beschermingsklasse IP	IP20

Product Details	
productbestanddeel	
<ul style="list-style-type: none"> hulpschakelaar 	Ja
productuitbreiding	hulpschakelaar

Aantal	
aantal foutsignaalshakelaars	0
aantal verbreekcontacten	1
aantal maakcontacten	1
aantal wisselcontacten	0

Aansluitingen	
aansluitbare kabeldoorsnede	0,5 ... 2,5 mm ²
aanhaalmoment / bij schroefaansluiting	0,5 N·m

aard van de aansluitbare kabeldoorsnede / bij AWG-leidingen	24 ... 12
---	-----------

Mechanical Design

hoogte	90 mm
breedte	9 mm
diepte	70 mm
nettogewicht	71 g
<ul style="list-style-type: none"> • tijdens bedrijf • tijdens opslag 	-25 ... +55 °C -40 ... +75 °C

Certificaten

Declaration of Conformity	Railway
----------------------------------	----------------



[Vibration and Shock](#)

Verdere informatie

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/nl/nl/Catalog/product?mlfb=5ST3010-2>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/nl/ps/5ST3010-2>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5ST3010-2

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



13 21



14 22

