

Fault signal contact with test and acknowledgment key 1 NO+1 NC, for miniature circuit breaker 5SL, 5SY, 5SP RCBO 5SU1, FI 5SV (for 5SU1 handle coupler 5ST3805-1 is required)



Versie	
productmerknaam	SETRON
productbenaming	foutsignaalschakelaar
uitvoering van het product	aanbouwbaar
elektrische levensduur (schakelcycli) / typisch	20 000
beschermingsklasse IP	IP20
Product Details	
productbestanddeel	
<ul style="list-style-type: none"> <li>foutsignaalschakelaar</li> </ul>	Ja
productuitbreiding	Storingssignaalschakelaar
Aantal	
aantal foutsignaalschakelaars	0
aantal verbreekcontacten	1
aantal maakcontacten	1
aantal wisselcontacten	0
Aansluitingen	
aansluitbare kabeldoorsnede	0,5 ... 2,5 mm <sup>2</sup>
aanhaalmoment / bij schroefaansluiting	0,5 N·m

aard van de aansluitbare kabeldoorsnede / bij AWG-leidingen	24 ... 12
---	-----------

### Mechanical Design

hoogte	90 mm
breedte	9 mm
diepte	70 mm
nettogewicht	72 g
<ul style="list-style-type: none"> <li>• tijdens bedrijf</li> <li>• tijdens opslag</li> </ul>	-25 ... +55 °C -40 ... +75 °C

### Certificaten

Declaration of Conformity

Railway

[Vibration and Shock](#)



EG-Konf.

### Verdere informatie

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/nl/nl/Catalog/product?mlfb=5ST3020-2>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/nl/ps/5ST3020-2>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5ST3020-2](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5ST3020-2)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



13 21



14 22

