

SIMBOX XL, 2-tier Wall recessed box flush-mounting 2-tier 24 MW
VPE 12 units



Figure similar

| Versie | |
|--|--|
| productmerksnaam | ALPHA |
| productbenaming | SIMBOX XL |
| uitvoering van de houderrail | DIN-rail 35 mm x 7,5 mm volgens DIN EN 60715 |
| uitvoering van de afdekkap | gesloten |
| uitvoering van het product / EMC-uitvoering | Geen |
| Voedingsspanning | |
| bedrijfsspanning / bij AC / nominale waarde | 400 V |
| Beschermingsklasse | |
| beschermingsklasse IP | IP30 |
| beschermingsniveau van de component | II |
| Elektriciteit | |
| stroom / bij AC / nominale waarde / maximaal | 63 A |
| Verschijning | |
| kleur | wit |

Product Details

| | |
|---|------|
| productbestanddeel | |
| • DIN-montagerail | Geen |
| • montageplaat | Geen |
| • transparante afdekkap | Geen |
| productuitbreiding / optioneel / aaneenschakeling | Geen |

Aantal

| | |
|--------------|---|
| aantal rijen | 1 |
|--------------|---|

Mechanical Design

| | |
|--------------------------------|-----------|
| hoogte | 373,6 mm |
| breedte | 340,6 mm |
| diepte | 90 mm |
| inbouwdiepte | 70 mm |
| aantal module-eenheden breedte | 12 |
| bevestigingswijze | spouwmuur |
| draaihoek van de deur | 125° |
| railhartafstand | 125 mm |
| nettogewicht | 821 g |
| materiaal / van de behuizing | kunststof |

Certificaten

General Product Approval



Verdere informatie

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/nl/nl/Catalog/product?mlfb=8GB5224-1KM01>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/nl/ps/8GB5224-1KM01>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8GB5224-1KM01

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

