

SR60 base DIAZED DII 3-pole 500 V AC DC for adaptor screw for 5/10 mm busbar thickness with clamp-type terminals



Figure similar

Versie	
productmerksnaam	SETRON
productbenaming	zekeringsysteem DIAZED
uitvoering van het product	SR60-SOKKEL
uitvoering van het smeltveiligheidsvoetstuk	passtuk
Algemene technische gegevens	
aantal polen	3
bouwgrootte van het beveiligingssysteem / volgens EN 60269-1	DII
Voedingsspanning	
stroom / bij AC / nominale waarde	25 A
voedingsspanning / bij AC / nominale waarde	500 V
Product Details	
productbestanddeel / afdekplaat	Geen
Mechanical Design	
hoogte	200 mm

breedte	42 mm
diepte	43,5 mm
nettogewicht	226 g
materiaal / van de behuizing	overige

Certificaten

referentiemarkering

- volgens EN 61346-2 F
- volgens IEC 81346-2:2009 F

Test Certificates

[Type Test Certificates/Test Report](#)

Verdere informatie

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/nl/nl/Catalog/product?mlfb=5SF6015>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/nl/ps/5SF6015>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SF6015

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

