

NEOZED, fuse base, D02, 1-pole, 63 A, Un AC: 400 V, Un DC: 250 V



Figure similar

Versie	
productmerksnaam	NEOZED
productbenaming	smeltveiligheidsvoetstuk
uitvoering van het product	NEOZED-inbouw-smeltveiligheidsvoetstuk
Uitvoering	Keramische sokkel met afdekking
Algemene technische gegevens	
aantal polen	1
bouwgrootte van het beveiligingssysteem / volgens EN 60269-1	D02
Voedingsspanning	
bedrijfsspanning / nominale waarde	400 V
Losbandigheid	
vermogensverlies [W] / bij nominale waarde stroom / bij AC / bij warme bedrijfstoestand / per pool	1 W
Hoofd-circuit	
bedrijfsstroom / nominale waarde	63 A

## Product Details

productbestanddeel / afdekplaat	Ja
---------------------------------	----

## Mechanical Design

hoogte	59 mm
breedte	26,8 mm
diepte	41 mm
bevestigingswijze	DIN-rail
nettogewicht	92 g
materiaal / van het D-smeltveiligheidsvoetstuk	porselein

## Certificaten

referentiemarkering	
• volgens EN 61346-2	F
• volgens IEC 81346-2:2009	F

General Product Approval	Declaration of Conformity	Test Certificates
--------------------------	---------------------------	-------------------



VDE



EG-Konf.

[Type Test Certificates/Test Report](#)

## Verdere informatie

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/nl/nl/Catalog/product?mlfb=5SG1653>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/nl/ps/5SG1653>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5SG1653](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SG1653)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://www.siemens.com/specifications>

