

SITOR cylindrical fuse link, 22x58 mm, 40 A, aR, Un AC: 690 V, Un DC: 700 V, DC according to UL



| Versie | |
|--|--------------------------------|
| productmerknaam | SETRON |
| productbenaming | cilindrisch SITOR-smeltpatroon |
| uitvoering van het product | DC volgens UL |
| Algemene technische gegevens | |
| bedrijfsklasse van de smeltpatroon | aR |
| grootte van de smeltpatroon | 22 x 58 mm |
| type spanning | AC |
| stroom / bij AC / nominale waarde | 40 A |
| voedingsspanning / bij DC | 700 V |
| bedrijfsspanning / nominale waarde | 690 V |
| Losbandigheid | |
| vermogensverlies [W] / bij nominale waarde stroom / bij AC / bij warme bedrijfstoestand / per pool | 8,5 W |
| Hoofd-circuit | |
| bedrijfsstroom / nominale waarde | 40 A |
| Product Details | |
| productbestanddeel / slagmelder | Geen |

| | |
|---------------|-------------------------------------|
| inbouwpositie | willekeurig, bij voorkeur verticaal |
| nettogewicht | 56 g |

Certificaten

referentiemarkering

- volgens EN 61346-2
- volgens IEC 81346-2:2009

F
F

General Product Approval

Declaration of Conformity



[Miscellaneous](#)



Verdere informatie

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/nl/nl/Catalog/product?mlfb=3NC2240>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/nl/ps/3NC2240>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NC2240

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



