

ALPHA 630, Floor-mounted cabinet, with open side wall, IP55,  
Protection class 1, H: 1950 mm, W: 1050 mm, T: 250 mm, RAL 7035



Versie	
productmerknaam	ALPHA 630
productbenaming	staande kast
uitvoering van het product	met open zijwand
oppervlaktebehandeling	poedergespoten

  

Beschermingsklasse	
beschermingsklasse IP	IP55
geschiktheid voor samenwerking / bliksembeveiliging	Ja
geschiktheid voor gebruik / voor gebruik buiten	Geen

  

Verschijning	
RAL-kleurnummer	RAL 7035
productbestanddeel	
• kabelinvoer	Ja
• montageplaat	Geen
productuitbreiding / optioneel / aaneenschakeling	Ja

  

Mechanical Design	
hoogte	1 950 mm
breedte	1 050 mm

diepte	250 mm
inbouwdiepte	250 mm
nettogewicht	64 kg
materiaal / van de behuizing	staal

## Certificaten

### referentiemarkering

- volgens EN 61346-2
- volgens IEC 81346-2:2009

U

UC

### General Product Approval

### Declaration of Conformity

### Test Certificates



[Miscellaneous](#)



EG-Konf.

[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)

## other

[Miscellaneous](#)

## Verdere informatie

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/nl/nl/Catalog/product?mfb=8GK1323-8KP43>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/nl/ps/8GK1323-8KP43>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=8GK1323-8KP43](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=8GK1323-8KP43)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://www.siemens.com/specifications>



