

SENTRON, cylindrical fuse holder, 10 x 38 mm, 1-pole, In: 30 A, Ue DC: 1000 V, LED Signal detector, for photovoltaic application



Versie	
productmerksnaam	SENTRON
productbenaming	cilindrische smeltpatroonhouder
uitvoering van het product	LED-LED-signaalmelder, voor fotovoltaïsche toepassing
Algemene technische gegevens	
aantal polen	1
bouwgrootte van de smeltpatroon	10x38 mm
Voedingsspanning	
stroom / bij AC / nominale waarde	30 A
bedrijfsspanning	
• bij DC / nominale waarde	1 000 V
beschermingsklasse IP	IP20
Mechanical Design	
hoogte	85 mm
breedte	18 mm
diepte	65 mm
nettogewicht	62 g

Certificaten

referentiemarkering

- volgens EN 61346-2
- volgens IEC 81346-2:2009

F

F

General Product Approval

Declaration of Con-
formity

other



CSA



UL



EG-Konf.

[Miscellaneous](#)

Verdere informatie

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/nl/nl/Catalog/product?mlfb=3NW7014-4>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/nl/ps/3NW7014-4>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW7014-4

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

