

SETRON, cylindrical fuse holder, 10x38 mm, 2-pole, In: 32 A, Un AC: 690 V, LED signal detector



Versie	
productmerksnaam	SETRON
productbenaming	cilindrische smeltpatroonhouder
uitvoering van het product	LED-signaalmelder
Algemene technische gegevens	
aantal polen	2
bouwgrootte van de smeltpatroon	10x38 mm
Voedingsspanning	
stroom / bij AC / nominale waarde	32 A
bedrijfsspanning	
• bij AC / nominale waarde	690 V
beschermingsklasse IP	IP20
Mechanical Design	
hoogte	81 mm
breedte	36 mm
diepte	64 mm
nettogewicht	136 g

Certificaten

referentiemarkering

- volgens EN 61346-2
- volgens IEC 81346-2:2009

F

F

General Product Approval

Declaration of Conformity



UR



EG-Konf.

Verdere informatie

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/nl/nl/Catalog/product?mlfb=3NW7024>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/nl/ps/3NW7024>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW7024

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





