

SETRON, cylindrical fuse holder, 14x51 mm, 2-pole, In: 50 A, Un AC: 690 V



### Versie

productmerknaam	SETRON
productbenaming	cilindrische smeltpatroonhouder

### Algemene technische gegevens

aantal polen	2
bouwgrootte van de smeltpatroon	14x51 mm

### Voedingsspanning

stroom / bij AC / nominale waarde	50 A
bedrijfsspanning	
• bij AC / nominale waarde	690 V
beschermingsklasse IP	IP20

### Mechanical Design

hoogte	90 mm
breedte	54 mm
diepte	70 mm
nettogewicht	214 g

### Certificaten

referentiemarkering

- volgens EN 61346-2
- volgens IEC 81346-2:2009

F

F

General Product Approval

Declaration of Conformity

Test Certificates



UR



EG-Konf.

[Miscellaneous](#)

Verdere informatie

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/nl/nl/Catalog/product?mfb=3NW7121>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/nl/ps/3NW7121>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=3NW7121](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=3NW7121)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>





