

SETRON, cylindrical fuse holder, 14x51 mm, 3-pole, In: 50 A, Un AC: 690 V



Versie	
productmerksnaam	SETRON
productbenaming	cilindrische smeltpatroonhouder
Algemene technische gegevens	
aantal polen	3
bouwgrootte van de smeltpatroon	14x51 mm
Voedingsspanning	
stroom / bij AC / nominale waarde	50 A
bedrijfsspanning	
• bij AC / nominale waarde	690 V
beschermingsklasse IP	IP20
Mechanical Design	
hoogte	90 mm
breedte	81 mm
diepte	70 mm
nettogewicht	306 g
Certificaten	

referentiemarkering

- volgens EN 61346-2
- volgens IEC 81346-2:2009

F  
F

General Product Approval	Declaration of Conformity	Test Certificates
--------------------------	---------------------------	-------------------



UR



EG-Konf.

[Miscellaneous](#)

Verdere informatie

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/nl/nl/Catalog/product?mfb=3NW7131>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/nl/ps/3NW7131>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=3NW7131](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=3NW7131)

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





