

SENTRON, cylindrical fuse holder, 22x58 mm, 1P+N, In: 100 A, Un AC: 690 V, LED signal detector



Versie	
productmerksnaam	SENTRON
productbenaming	cilindrische smeltpatroonhouder
uitvoering van het product	LED-signaalmelder
Algemene technische gegevens	
aantal polen	2
aantal polen / opmerking	1P+N
bouwgrootte van de smeltpatroon	22x58 mm
Voedingsspanning	
stroom / bij AC / nominale waarde	100 A
bedrijfsspanning	
• bij AC / nominale waarde	690 V
beschermingsklasse IP	IP20
Mechanical Design	
hoogte	117 mm
breedte	72 mm
diepte	70 mm
nettogewicht	360 g

## Certificaten

### referentiemarkering

- volgens EN 61346-2
- volgens IEC 81346-2:2009

F  
F

## Declaration of Conformity



EG-Konf.

## Verdere informatie

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/nl/nl/Catalog/product?mfb=3NW7252>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/nl/ps/3NW7252>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=3NW7252](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=3NW7252)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://www.siemens.com/specifications>





