

SETRON, cylindrical fuse holder, 8x32 mm, 3P+N, In: 20 A, Un AC: 400 V, LED signal detector



### Versie

productmerksnaam	SETRON
productbenaming	cilindrische smeltpatroonhouder
uitvoering van het product	LED-signaalmelder

### Algemene technische gegevens

aantal polen	4
aantal polen / opmerking	3P+N
bouwgrootte van de smeltpatroon	8x32 mm

### Voedingsspanning

stroom / bij AC / nominale waarde	20 A
bedrijfsspanning	
• bij AC / nominale waarde	400 V
beschermingsklasse IP	IP20

### Mechanical Design

hoogte	81 mm
breedte	54 mm
diepte	64 mm
nettogewicht	218 g

## Certificaten

### referentiemarkering

- volgens EN 61346-2
- volgens IEC 81346-2:2009

F  
F

## Declaration of Conformity



EG-Konf.

## Verdere informatie

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/nl/nl/Catalog/product?mfb=3NW7364>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/nl/ps/3NW7364>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=3NW7364](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=3NW7364)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://www.siemens.com/specifications>





