

ALPHA 630, Floor-mounted cabinet, IP43, Protection class 1, H: 1950 mm, W: 1300 mm, T: 210 mm, RAL 7035, incl. flange in roof



Versie	
productmerknaam	ALPHA 630
productbenaming	staande kast
oppervlaktebehandeling	poedergespoten
Beschermingsklasse	
beschermingsklasse IP	IP43
geschiktheid voor samenwerking / bliksembeveiliging	Ja
geschiktheid voor gebruik / voor gebruik buiten	Geen
Verschijning	
RAL-kleurnummer	RAL 7035
productbestanddeel	
<ul style="list-style-type: none"> • kabelinvoer • montageplaat 	<p>Ja</p> <p>Geen</p>
speciale producteigenschap	incl. flens in het dak
productuitbreiding / optioneel / aaneenschakeling	Ja
Mechanical Design	
hoogte	1 950 mm
breedte	1 300 mm

diepte	210 mm
inbouwdiepte	210 mm
nettogewicht	71 kg
materiaal / van de behuizing	staal

Certificaten

referentiemarkering

- volgens EN 61346-2
- volgens IEC 81346-2:2009

U

UC

General Product Approval

Test Certificates

other



[Special Test Certificate](#)

[Miscellaneous](#)

Verdere informatie

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/nl/nl/Catalog/product?mlfb=8GK1322-8KA52>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/nl/ps/8GK1322-8KA52>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8GK1322-8KA52

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



