

ALPHA 630, Floor-mounted cabinet, IP55, Protection class 1, H: 1950 mm, W: 300 mm, T: 320 mm, RAL 7035



Versie	
productmerknaam	ALPHA 630
productbenaming	staande kast
oppervlaktebehandeling	poedergespoten
Beschermingsklasse	
beschermingsklasse IP	IP55
geschiktheid voor samenwerking / bliksembeveiliging	Ja
geschiktheid voor gebruik / voor gebruik buiten	Geen
Verschijning	
RAL-kleurnummer	RAL 7035
productbestanddeel	
<ul style="list-style-type: none"> <li>• kabelinvoer</li> <li>• montageplaat</li> </ul>	<p>Ja</p> <p>Geen</p>
productuitbreiding / optioneel / aaneenschakeling	Ja
Mechanical Design	
hoogte	1 950 mm
breedte	300 mm
diepte	320 mm

inbouwdiepte	320 mm
nettogewicht	32,5 kg
materiaal / van de behuizing	staal

## Certificaten

referentiemarkering

- volgens EN 61346-2
- volgens IEC 81346-2:2009

U

UC

**General Product Approval**

**Declaration of  
Conformity**

**Test Certificates**



VDE

[Miscellaneous](#)



EG-Konf.

[Special Test Certificate](#)

[Type Test Certificates/Test Report](#)

**other**

[Miscellaneous](#)

## Verdere informatie

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/nl/nl/Catalog/product?mlfb=8GK1323-8KN14>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/nl/ps/8GK1323-8KN14>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8GK1323-8KN14](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8GK1323-8KN14)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



