

ALPHA 630, Floor-mounted cabinet, with open side wall, IP55,
Protection class 1, H: 1950 mm, W: 1050 mm, T: 320 mm, RAL 7035



Versie

productmerknaam	ALPHA 630
productbenaming	staande kast
uitvoering van het product	met open zijwand
oppervlaktebehandeling	poedergespoten

Beschermingsklasse

beschermingsklasse IP	IP55
geschiktheid voor samenwerking / bliksembeveiliging	Ja
geschiktheid voor gebruik / voor gebruik buiten	Geen

Verschuiving

RAL-kleurnummer	RAL 7035
productbestanddeel	
• kabelinvoer	Ja
• montageplaat	Geen
productuitbreiding / optioneel / aaneenschakeling	Ja

Mechanical Design

hoogte	1 950 mm
breedte	1 050 mm

diepte	320 mm
inbouwdiepte	320 mm
nettogewicht	66 kg
materiaal / van de behuizing	staal

Certificaten

referentiemarkering

- volgens EN 61346-2
- volgens IEC 81346-2:2009

U

UC

General Product Approval

Declaration of Conformity

Test Certificates



[Miscellaneous](#)



EG-Konf.

[Special Test Certificate](#)

[Type Test Certificates/Test Report](#)

other

[Miscellaneous](#)

Verdere informatie

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/nl/nl/Catalog/product?mfb=8GK1323-8KP44>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/nl/ps/8GK1323-8KP44>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=8GK1323-8KP44

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



