

SENTRON, fuse holder, Class CC, 2-pole, In: 30 A, Un AC: 600 V, respect national installation rules!



Versie	
productmerksnaam	SENTRON
productbenaming	smeltpatroonhouder
Algemene technische gegevens	
aantal polen	2
bouwgrootte van de smeltpatroon	Class CC
Voedingsspanning	
stroom / bij AC / nominale waarde	30 A
bedrijfsspanning	
• bij AC / nominale waarde	600 V
beschermingsklasse IP	IP20
Mechanical Design	
hoogte	85 mm
breedte	36 mm
diepte	65 mm
nettogewicht	105 g
Certificaten	

referentiemarkering

- volgens EN 61346-2
- volgens IEC 81346-2:2009

F

F

General Product Approval

Declaration of Conformity



CSA



UL



UR



EG-Konf.

Verdere informatie

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/nl/nl/Catalog/product?mlfb=3NW7523-0HG>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/nl/ps/3NW7523-0HG>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NW7523-0HG](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW7523-0HG)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>





