

SETRON, cylindrical fuse link, Class CC, 7.5 A, time-lag, Un AC: 600 V, respect national installation rules!



### Versie

productmerksnaam	SETRON
productbenaming	cilindrisch smeltpatroon

### Algemene technische gegevens

bedrijfsklasse van de smeltpatroon	traag
grootte van de smeltpatroon	Class CC
type spanning	AC
stroom / bij AC / nominale waarde	7,5 A
bedrijfsspanning / nominale waarde	600 V

### Hoofd-circuit

bedrijfsstroom / nominale waarde	7,5 A
----------------------------------	-------

### Product Details

productbestanddeel / slagmelder	Geen
inbouwpositie	willekeurig, bij voorkeur verticaal
nettogewicht	7 g

### Certificaten

referentiemarkering	
---------------------	--

- volgens EN 61346-2
- volgens IEC 81346-2:2009

F

F

### General Product Approval

### Declaration of Conformity



CSA



UL



EG-Konf.

### Verdere informatie

#### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

#### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/nl/nl/Catalog/product?mlfb=3NW1075-0HG>

#### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/nl/ps/3NW1075-0HG>

#### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NW1075-0HG](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW1075-0HG)

#### CAX-Online-Generator

<http://www.siemens.com/cax>

#### Tender specifications

<http://www.siemens.com/specifications>

