

SENTRON, cylindrical fuse link, Class CC, 10 A, time-lag, Un AC:  
600 V, respect national installation rules!



Versie	
productmerksnaam	SENTRON
productbenaming	cilindrisch smeltpatroon
Algemene technische gegevens	
bedrijfsklasse van de smeltpatroon	traag
grootte van de smeltpatroon	Class CC
type spanning	AC
stroom / bij AC / nominale waarde	10 A
bedrijfsspanning / nominale waarde	600 V
Hoofd-circuit	
bedrijfsstroom / nominale waarde	10 A
Product Details	
productbestanddeel / slagmelder	Geen
inbouwpositie	willekeurig, bij voorkeur verticaal
nettogewicht	11 g
Certificaten	
referentiemarkering	

- volgens EN 61346-2
- volgens IEC 81346-2:2009

F

F

### General Product Approval

### Declaration of Conformity



### Verdere informatie

#### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

#### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/nl/nl/Catalog/product?mfb=3NW1100-0HG>

#### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/nl/ps/3NW1100-0HG>

#### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=3NW1100-0HG](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=3NW1100-0HG)

#### CAX-Online-Generator

<http://www.siemens.com/cax>

#### Tender specifications

<http://www.siemens.com/specifications>

