

SENTRON, cylindrical fuse link, Class CC, 4 A, time-lag, current-limiting, Un AC: 600 V, respect national installation rules!



Versie	
productmerknaam	SENTRON
productbenaming	cilindrisch smeltpatroon
Algemene technische gegevens	
bedrijfsklasse van de smeltpatroon	traag, stroombegrenzend
grootte van de smeltpatroon	Class CC
type spanning	AC
stroom / bij AC / nominale waarde	4 A
bedrijfsspanning / nominale waarde	600 V
Hoofd-circuit	
bedrijfsstroom / nominale waarde	4 A
Product Details	
productbestanddeel / slagmelder	Geen
inbouwpositie	willekeurig, bij voorkeur verticaal
nettogewicht	1 g
Certificaten	
referentiemarkering	

- volgens EN 61346-2
- volgens IEC 81346-2:2009

F

F

### General Product Approval

### Declaration of Conformity



### Verdere informatie

#### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

#### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/nl/nl/Catalog/product?mfb=3NW3040-0HG>

#### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/nl/ps/3NW3040-0HG>

#### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=3NW3040-0HG](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=3NW3040-0HG)

#### CAX-Online-Generator

<http://www.siemens.com/cax>

#### Tender specifications

<http://www.siemens.com/specifications>

