

Class J fuse link 25 A 600 V time-lag, respect national installation rules!



Versie	
productmerksnaam	SETRON
productbenaming	cilindrisch smeltpatroon
uitvoering van het product	cilindrische uitvoering
Algemene technische gegevens	
bedrijfsklasse van de smeltpatroon	traag
grootte van de smeltpatroon	Class J
type spanning	AC
stroom / bij AC / nominale waarde	25 A
voedingsspanning / bij DC	300 V
bedrijfsspanning / nominale waarde	600 V
Hoofd-circuit	
bedrijfsstroom / nominale waarde	25 A
Product Details	
productbestanddeel / slagmelder	Geen
inbouwpositie	willekeurig, bij voorkeur verticaal
nettogewicht	46 g

## Certificaten

### referentiemarkering

- volgens EN 61346-2
- volgens IEC 81346-2:2009

F  
F

## General Product Approval



CSA



UL

## Verdere informatie

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/nl/nl/Catalog/product?mlfb=3NW4110-2HG>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/nl/ps/3NW4110-2HG>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NW4110-2HG](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW4110-2HG)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://www.siemens.com/specifications>



