

SITOR cylindrical fuse link, 14x51 mm, 40 A, aR, Un AC: 690 V, Un DC: 600 V, DC according to UL, Striker indicator



Versie

productmerksnaam	SENTRON
productbenaming	cilindrisch SITOR-smeltpatroon
uitvoering van het product	DC volgens UL
uitvoering van de verklikker	slagstift-verklikker

Algemene technische gegevens

bedrijfsklasse van de smeltpatroon	aR
grootte van de smeltpatroon	14 x 51 mm
type spanning	AC
stroom / bij AC / nominale waarde	40 A
voedingsspanning / bij DC	600 V
bedrijfsspanning / nominale waarde	690 V

Losbandigheid

vermogensverlies [W] / bij nominale waarde stroom / bij AC / bij warme bedrijfstoestand / per pool	8 W
--	-----

Hoofd-circuit

bedrijfsstroom / nominale waarde	40 A
----------------------------------	------

Product Details

productbestanddeel / slagmelder	Ja
inbouwpositie	willekeurig, bij voorkeur verticaal
nettogewicht	23 g

Certificaten

referentiemarkering

- volgens EN 61346-2
- volgens IEC 81346-2:2009

F
F

General Product Approval

Declaration of Conformity



UR

[Miscellaneous](#)



EG-Konf.

Verdere informatie

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/nl/nl/Catalog/product?mfb=3NC1440-5>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/nl/ps/3NC1440-5>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=3NC1440-5

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



