

SETRON, cylindrical fuse holder, 22x58 mm, 3-pole, In: 100 A, Un AC: 690 V



Versie	
productmerksnaam	SETRON
productbenaming	cilindrische smeltpatroonhouder
Algemene technische gegevens	
aantal polen	3
bouwgrootte van de smeltpatroon	22x58 mm
Voedingsspanning	
stroom / bij AC / nominale waarde	100 A
bedrijfsspanning	
• bij AC / nominale waarde	690 V
beschermingsklasse IP	IP20
Mechanical Design	
hoogte	117 mm
breedte	108 mm
diepte	70 mm
nettogewicht	503 g
Certificaten	

referentiemarkering

- volgens EN 61346-2
- volgens IEC 81346-2:2009

F

F

Declaration of Conformity

Test Certificates



EG-Konf.

[Miscellaneous](#)

## Verdere informatie

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/nl/nl/Catalog/product?mlfb=3NW7231>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/nl/ps/3NW7231>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NW7231](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW7231)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>





