

SITOR cylindrical fuse link, 22x58 mm, 25 A, aR, Un AC: 690 V, Un DC: 500 V, DC according to UL, Striker indicator



Versie	
productmerknaam	SENTRON
productbenaming	cilindrisch SITOR-smeltpatroon
uitvoering van het product	DC volgens UL
uitvoering van de verklikker	slagstift-verklikker
Algemene technische gegevens	
bedrijfsklasse van de smeltpatroon	aR
grootte van de smeltpatroon	22 x 58 mm
type spanning	AC
stroom / bij AC / nominale waarde	25 A
voedingsspanning / bij DC	500 V
bedrijfsspanning / nominale waarde	690 V
Losbandigheid	
vermogensverlies [W] / bij nominale waarde stroom / bij AC / bij warme bedrijfstoestand / per pool	6 W
Hoofd-circuit	
bedrijfsstroom / nominale waarde	25 A
Product Details	

productbestanddeel / slagmelder	Ja
inbouwpositie	willekeurig, bij voorkeur verticaal
nettogewicht	41 g

Certificaten

referentiemarkering

- volgens EN 61346-2
- volgens IEC 81346-2:2009

F

F

General Product Approval

Declaration of Conformity



UR

[Miscellaneous](#)



EG-Konf.

Verdere informatie

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/nl/nl/Catalog/product?mfb=3NC2225-5>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/nl/ps/3NC2225-5>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=3NC2225-5

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



