

SITOR cylindrical fuse link, 22x127 mm, 40 A, gR, Un AC: 1500 V,
Un DC: 1000 V



Versie	
productmerksnaam	SENTRON
productbenaming	cilindrisch SITOR-smeltpatroon
Algemene technische gegevens	
bedrijfsklasse van de smeltpatroon	gR
grootte van de smeltpatroon	22x127 mm
type spanning	AC
stroom / bij AC / nominale waarde	40 A
voedingsspanning / bij DC	1 000 V
bedrijfsspanning / nominale waarde	1 500 V
Hoofd-circuit	
bedrijfsstroom / nominale waarde	40 A
Product Details	
productbestanddeel / slagmelder	Geen
inbouwpositie	willekeurig, bij voorkeur verticaal
nettogewicht	96 g
Certificaten	

referentiemarkering

- volgens EN 61346-2
- volgens IEC 81346-2:2009

F

F

General Product Approval

[Miscellaneous](#)

Verdere informatie

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/nl/nl/Catalog/product?mlfb=3NC2340-0MK>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/nl/ps/3NC2340-0MK>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NC2340-0MK

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



