



Moduł do parametryzacji DE1

Typ DXE-EXT-SET
Catalog No. 174621
Alternate Catalog No. DXE-EXT-SET
No.

Program dostaw

Opis		z przełącznikiem wybierakowym czasu rampy i trybu pracy z potencjometrem do ochrony silnika i częstotliwości stałej
Stosowane do		DE1, DE11
Sposób podłączenia		Moduł wtykowy (z przodu)

Świadectwo typu zgodnie z IEC/EN 61439

Dane techniczne dla zaświadczenia rodzaju konstrukcji		
Robocza temperatura otoczenia min.	°C	-10
Robocza temperatura otoczenia maks.	°C	50

Dane techniczne zgodne z ETIM 7.0

Urządzenia niskonapięciowe (EG000017) / Akcesoria do przemienników częstotliwości (EC002025)		
Elektrotechnika, automatyzacja i technologia / Napęd elektryczny / Falownik / Static frequency converter (accessory) (ecl@ss10.0.1-27-02-31-92 [AFR303003])		
Rodzaj akcesorium		Inne

Aprobaty

Product Standards		UL 508C; CSA-C22.2 No. 274; IEC/EN61800-3; IEC/EN61800-5; CE marking
UL File No.		E172143
UL Category Control No.		NMMS, NMMS7
CSA File No.		UL report applies to both US and Canada
North America Certification		UL recognized, certified by UL for use in Canada
Specially designed for North America		No
Suitable for		Branch circuits

Wymiary

