

SETRON, cylindrical fuse holder, 10x38 mm, 2-pole, In: 32 A, Un AC: 690 V, LED signal detector



Wersja	
Nazwa markowa produktu	SETRON
oznaczenie produktu	Uchwyt bezpiecznika cylindrycznego
wykonanie produktu	Sygnalizator LED
Ogólne dane techniczne	
liczba biegunów	2
wielkość wkładki bezpiecznikowej	10 x 38 mm
Napięcie zasilania	
prąd / przy AC / wartość znamionowa	32 A
napięcie robocze	690 V
• przy AC / wartość znamionowa	
Stopień ochrony IP	IP20
Konstrukcja mechaniczna	
wysokość	81 mm
szerokość	36 mm
głębokość	64 mm
masa netto	136 g

Certyfikaty

oznaczenie środków roboczych

- zgodnie z DIN EN 61246-2
- zgodnie z IEC 81346-2:2009

F

F

General Product Approval

Declaration of Conformity



UR



EG-Konf.

Więcej informacji

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW7024>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pl/ps/3NW7024>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW7024

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





