

SETRON, cylindrical fuse holder, 14x51 mm, 1-pole, In: 50 A, Un AC: 690 V



Wersja	
Nazwa markowa produktu	SETRON
oznaczenie produktu	Uchwyt bezpiecznika cylindrycznego
Ogólne dane techniczne	
liczba biegunów	1
wielkość wkładki bezpiecznikowej	14x51 mm
Napięcie zasilania	
prąd / przy AC / wartość znamionowa	50 A
napięcie robocze	690 V
• przy AC / wartość znamionowa	
Stopień ochrony IP	IP20
Konstrukcja mechaniczna	
wysokość	90 mm
szerokość	27 mm
głębokość	70 mm
masa netto	106 g
Certyfikaty	

oznaczenie środków roboczych

- zgodnie z DIN EN 61246-2
- zgodnie z IEC 81346-2:2009

F

F

**General Product Approval**

**Declaration of Conformity**

**Test Certificates**



UR



EG-Konf.

[Miscellaneous](#)

## Więcej informacji

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW7111>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/pl/ps/3NW7111>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NW7111](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW7111)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>





