

SETRON, cylindrical fuse holder, 14x51 mm, 2-pole, In: 50 A, Un AC: 690 V



Wersja

Nazwa markowa produktu	SETRON
oznaczenie produktu	Uchwyt bezpiecznika cylindrycznego

Ogólne dane techniczne

liczba biegunów	2
wielkość wkładki bezpiecznikowej	14x51 mm

Napięcie zasilania

prąd / przy AC / wartość znamionowa	50 A
napięcie robocze	690 V
<ul style="list-style-type: none"> przy AC / wartość znamionowa 	690 V
Stopień ochrony IP	IP20

Konstrukcja mechaniczna

wysokość	90 mm
szerokość	54 mm
głębokość	70 mm
masa netto	214 g

Certyfikaty

oznaczenie środków roboczych

- zgodnie z DIN EN 61246-2
- zgodnie z IEC 81346-2:2009

F

F

General Product Approval

Declaration of Conformity

Test Certificates



UR



EG-Konf.

[Miscellaneous](#)

Więcej informacji

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW7121>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pl/ps/3NW7121>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW7121

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





