

SETRON, cylindrical fuse holder, 14x51 mm, 3-pole, In: 50 A, Un AC: 690 V, LED signal detector



Wersja	
Nazwa markowa produktu	SETRON
oznaczenie produktu	Uchwyt bezpiecznika cylindrycznego
wykonanie produktu	Sygnalizator LED
Ogólne dane techniczne	
liczba biegunów	3
wielkość wkładki bezpiecznikowej	14x51 mm
Napięcie zasilania	
prąd / przy AC / wartość znamionowa	50 A
napięcie robocze	690 V
• przy AC / wartość znamionowa	
Stopień ochrony IP	IP20
Konstrukcja mechaniczna	
wysokość	90 mm
szerokość	81 mm
głębokość	70 mm
masa netto	327 g

## Certyfikaty

oznaczenie środków roboczych

- zgodnie z DIN EN 61246-2
- zgodnie z IEC 81346-2:2009

F

F

General Product Approval

Declaration of Conformity



UR



EG-Konf.

## Więcej informacji

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW7132>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/pl/ps/3NW7132>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NW7132](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW7132)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>





