

SETRON, cylindrical fuse holder, 22x58 mm, 1P+N, In: 100 A, Un AC: 690 V



Wersja	
Nazwa markowa produktu	SETRON
oznaczenie produktu	Uchwyt bezpiecznika cylindrycznego
Ogólne dane techniczne	
liczba biegunów	2
liczba biegunów / uwaga	1P+N
wielkość wkładki bezpiecznikowej	22x58 mm
Napięcie zasilania	
prąd / przy AC / wartość znamionowa	100 A
napięcie robocze	
• przy AC / wartość znamionowa	690 V
Stopień ochrony IP	IP20
Konstrukcja mechaniczna	
wysokość	117 mm
szerokość	72 mm
głębokość	70 mm
masa netto	365 g

Certyfikaty

oznaczenie środków roboczych

- zgodnie z DIN EN 61246-2
- zgodnie z IEC 81346-2:2009

F

F

Declaration of Conformity

Test Certificates



EG-Konf.

[Miscellaneous](#)

Więcej informacji

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW7251>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pl/ps/3NW7251>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW7251

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





