

SETRON, cylindrical fuse holder, 8x32 mm, 3P+N, In: 20 A, Un AC: 400 V



### Wersja

Nazwa markowa produktu	SETRON
oznaczenie produktu	Uchwyt bezpiecznika cylindrycznego

### Ogólne dane techniczne

liczba biegunów	4
liczba biegunów / uwaga	3P+N
wielkość wkładki bezpiecznikowej	8x32 mm

### Napięcie zasilania

prąd / przy AC / wartość znamionowa	20 A
napięcie robocze	400 V
• przy AC / wartość znamionowa	
Stopień ochrony IP	IP20

### Konstrukcja mechaniczna

wysokość	81 mm
szerokość	54 mm
głębokość	64 mm
masa netto	210 g

## Certyfikaty

oznaczenie środków roboczych

- zgodnie z DIN EN 61246-2
- zgodnie z IEC 81346-2:2009

F  
F

## Declaration of Conformity



EG-Konf.

## Więcej informacji

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW7363>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/pl/ps/3NW7363>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NW7363](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW7363)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>





