

ALPHA 630, Floor-mounted cabinet, IP43, Protection class 1, H:
1950 mm, W: 1300 mm, T: 210 mm, RAL 7035, incl. flange in roof



Wersja

Nazwa markowa produktu	ALPHA 630
oznaczenie produktu	Szafa stojąca
obróbka powierzchniowa	powlekany proszkowo

Klasa ochrony

Stopień ochrony IP	IP43
możliwość współdziałania / ochrona odgromowa	Tak
możliwość zastosowania / do użytku zewnętrznego	Nigdy
element składowy produktu	
• wprowadzenie kabla	Tak
• płyta montażowa	Nigdy
specjalna właściwość produktu	łącznie z kołnierzem w dachu
rozszerzenie produktu / opcjonalny / ustawienie szeregowo	Tak

Konstrukcja mechaniczna

wysokość	1 950 mm
szerokość	1 300 mm
głębokość	210 mm

głębokość montażowa	210 mm
masa netto	71 kg
materiał / obudowy	Stal

Certyfikaty

oznaczenie środków roboczych

- zgodnie z DIN EN 61246-2
- zgodnie z IEC 81346-2:2009

U

UC

General Product Approval

Test Certificates

other



[Special Test Certificate](#)

[Miscellaneous](#)

Więcej informacji

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8GK1322-8KA52>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pl/ps/8GK1322-8KA52>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8GK1322-8KA52

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



