

ALPHA 630, Floor-mounted cabinet, with open side wall, IP55,  
Protection class 1, H: 1950 mm, W: 1050 mm, T: 320 mm, RAL 7035



Wersja	
Nazwa markowa produktu	ALPHA 630
oznaczenie produktu	Szafa stojąca
wykonanie produktu	z otwartą ścianą boczną
obróbka powierzchniowa	powlekany proszkowo

Klasa ochrony	
Stopień ochrony IP	IP55
możliwość współdziałania / ochrona odgromowa	Tak
możliwość zastosowania / do użytku zewnętrznego	Nigdy
element składowy produktu	
• wprowadzenie kabla	Tak
• płyta montażowa	Nigdy
rozszerzenie produktu / opcjonalny / ustawienie szeregowo	Tak

Konstrukcja mechaniczna	
wysokość	1 950 mm
szerokość	1 050 mm
głębokość	320 mm

głębokość montażowa	320 mm
masa netto	66 kg
materiał / obudowy	Stal

## Certyfikaty

oznaczenie środków roboczych

- zgodnie z DIN EN 61246-2
- zgodnie z IEC 81346-2:2009

U  
UC

**General Product Approval**

**Declaration of  
Conformity**

**Test Certificates**



[Miscellaneous](#)



[Special Test Certificate](#)

[Type Test Certificates/Test Report](#)

**other**

[Miscellaneous](#)

## Więcej informacji

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8GK1323-8KP44>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/pl/ps/8GK1323-8KP44>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8GK1323-8KP44](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8GK1323-8KP44)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



