

ALPHA 630, Floor-mounted cabinet, IP43, Protection class 2, H:
1950 mm, W: 300 mm, T: 210 mm, RAL 7035



Wersja	
Nazwa markowa produktu	ALPHA 630
oznaczenie produktu	Szafa stojąca
obróbka powierzchniowa	powlekany proszkowo
Klasa ochrony	
Stopień ochrony IP	IP43
możliwość współdziałania / ochrona odgromowa	Tak
możliwość zastosowania / do użytku zewnętrznego	Nigdy
element składowy produktu	
• wprowadzenie kabla	Tak
• płyta montażowa	Nigdy
rozszerzenie produktu / opcjonalny / ustawienie szeregowe	Tak
Konstrukcja mechaniczna	
wysokość	1 950 mm
szerokość	300 mm
głębokość	210 mm
głębokość montażowa	210 mm

masa netto	30,3 kg
materiał / obudowy	Stal

Certyfikaty

oznaczenie środków roboczych

- zgodnie z DIN EN 61246-2
- zgodnie z IEC 81346-2:2009

U

UC

General Product Approval	Test Certificates	other
---------------------------------	--------------------------	--------------



[Special Test Certificate](#)

[Miscellaneous](#)

Więcej informacji

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8GK1332-8KA12>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pl/ps/8GK1332-8KA12>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8GK1332-8KA12

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



