

ALPHA 630, Floor-mounted cabinet, IP55, Protection class 2, H: 1950 mm, W: 800 mm, T: 320 mm, RAL 7035



Wersja	
Nazwa markowa produktu	ALPHA 630
oznaczenie produktu	Szafa stojąca
obróbka powierzchniowa	powlekany proszkowo
Klasa ochrony	
Stopień ochrony IP	IP55
możliwość współdziałania / ochrona odgromowa	Tak
możliwość zastosowania / do użytku zewnętrznego	Nigdy
element składowy produktu	
• wprowadzenie kabla	Tak
• płyta montażowa	Nigdy
rozszerzenie produktu / opcjonalny / ustawienie szeregowe	Tak
Konstrukcja mechaniczna	
wysokość	1 950 mm
szerokość	800 mm
głębokość	320 mm
głębokość montażowa	320 mm

masa netto	62 kg
materiał / obudowy	Stal

## Certyfikaty

oznaczenie środków roboczych

- zgodnie z DIN EN 61246-2
- zgodnie z IEC 81346-2:2009

U

UC

General Product Approval

Declaration of  
Conformity

Test Certificates



VDE

[Miscellaneous](#)



EG-Konf.

[Special Test Certificate](#)

[Type Test Certificates/Test Report](#)

other

[Miscellaneous](#)

## Więcej informacji

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8GK1333-8KN34>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/pl/ps/8GK1333-8KN34>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8GK1333-8KN34](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8GK1333-8KN34)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



