

ALPHA 630, Floor-mounted cabinet, IP55, Protection class 2, H:  
1950 mm, W: 1300 mm, T: 250 mm, RAL 7035



Wersja	
Nazwa markowa produktu	ALPHA 630
oznaczenie produktu	Szafa stojąca
obróbka powierzchniowa	powlekany proszkowo

  

Klasa ochrony	
Stopień ochrony IP	IP55
możliwość współdziałania / ochrona odgromowa	Tak
możliwość zastosowania / do użytku zewnętrznego	Nigdy
element składowy produktu	
• wprowadzenie kabla	Tak
• płyta montażowa	Nigdy
rozszerzenie produktu / opcjonalny / ustawienie szeregowe	Tak

  

Konstrukcja mechaniczna	
wysokość	1 950 mm
szerokość	1 300 mm
głębokość	250 mm
głębokość montażowa	250 mm

masa netto	74,3 kg
materiał / obudowy	Stal

## Certyfikaty

oznaczenie środków roboczych

- zgodnie z DIN EN 61246-2
- zgodnie z IEC 81346-2:2009

U

UC

<b>General Product Approval</b>	<b>Declaration of Conformity</b>	<b>Test Certificates</b>
---------------------------------	----------------------------------	--------------------------



VDE



[Miscellaneous](#)



EG-Konf.

[Special Test Certificate](#)

[Type Test Certificates/Test Report](#)

## other

[Miscellaneous](#)

## Więcej informacji

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8GK1333-8KN53>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/pl/ps/8GK1333-8KN53>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8GK1333-8KN53](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8GK1333-8KN53)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



