

SITOR cylindrical fuse link, 14x51 mm, 25 A, aR, Un AC: 690 V, Un DC: 600 V, DC according to UL, Striker indicator



Wersja

Nazwa markowa produktu	SETRON
oznaczenie produktu	Wkładka bezpiecznika cylindrycznego SITOR
wykonanie produktu	DC zgodnie z UL
wykonanie wskaźnika zadziałania	Wybijak-wskaźnik zadziałania

Ogólne dane techniczne

charakterystyka wkładki bezpiecznikowej	aR
wielkość wkładki bezpiecznikowej	14x51 mm
rodzaj napięcia	AC
prąd / przy AC / wartość znamionowa	25 A
napięcie zasilające / przy DC	600 V
napięcie robocze / wartość znamionowa	690 V

Rozpraszanie

Strata mocy [W] / w przypadku wartości znamionowej prądu / w przypadku AC / w stanie rozgrzanym / na biegun	7 W
---	-----

Obwód główny

prąd roboczy / wartość nominalna	25 A
----------------------------------	------

Szczegóły produktu

element składowy produktu / sygnalizator uderzenia	Tak
pozycja montażowa	dowolnie, najlepiej pionowo
masa netto	21 g

Certyfikaty

oznaczenie środków roboczych	
<ul style="list-style-type: none">• zgodnie z DIN EN 61246-2	F
<ul style="list-style-type: none">• zgodnie z IEC 81346-2:2009	F

General Product Approval

Declaration of Conformity



UR

[Miscellaneous](#)



EG-Konf.

Więcej informacji

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NC1425-5>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pl/ps/3NC1425-5>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NC1425-5

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



