

SETRON, cylindrical fuse link, Class CC, 4 A, time-lag, current-limiting, Un AC: 600 V, respect national installation rules!



Wersja	
Nazwa markowa produktu	SETRON
oznaczenie produktu	Wkładka bezpiecznika cylindrycznego
Ogólne dane techniczne	
charakterystyka wkładki bezpiecznikowej	zwłoczny, ograniczający prąd
wielkość wkładki bezpiecznikowej	Class CC
rodzaj napięcia	AC
prąd / przy AC / wartość znamionowa	4 A
napięcie robocze / wartość znamionowa	600 V
Obwód główny	
prąd roboczy / wartość nominalna	4 A
Szczegóły produktu	
element składowy produktu / sygnalizator uderzenia	Nigdy
pozycja montażowa	dowolnie, najlepiej pionowo
masa netto	1 g
Certyfikaty	
oznaczenie środków roboczych	

- zgodnie z DIN EN 61246-2
- zgodnie z IEC 81346-2:2009

F

F

General Product Approval

Declaration of Conformity



CSA

UL

EG-Konf.

Więcej informacji

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW3040-0HG>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pl/ps/3NW3040-0HG>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW3040-0HG

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

