

SIMATIC DP, Power Rail Booster Signal amplifier for the transfer of the PROFIBUS DP via sliding contacts max. 500 Kbit/s



Figure similar

Supply voltage

permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V

Input current

Current consumption, max.	1.2 A
---------------------------	-------

Power loss

Power loss, max.	20 W
------------------	------

Dimensions

Width	90 mm
Height	132 mm
Depth	67.5 mm

last modified: 09/11/2019